



# Vertical Pin Standoff Bracket, 60" Two-Phase

by CHANCE Utility  
Catalog ID: 2SBH60VV1

60" Heavy Duty Fiberglass Two-Phase Vertical Pin Standoff Bracket with  
1" Plastisol Coated Threads



\* Representative image

## Product Details

### General

Description - End Fitting	Vertical Pin
Material - Threads	1" Plastisol Threads
Strength Rating - Minimum Ultimate, Longitudinal (L)	1200 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1950 lb
UPC	096359069270

### Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	60 in
Length	60.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 5.00 in</li><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	26.1 lb

### Logistics

Pallet Quantity	24 EA
Standard Package	4

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)