



15° 2-Position Cutout / Arrester Standoff Bracket, 36" 2-Phase

by CHANCE Utility
Catalog ID: 2SBM36AMTAMT

36 Medium Duty 15° 2-Position Two-Phase Cutout / Arrester Standoff Bracket



Product Details

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	900 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359486527

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	12.6 lb

Electrical Ratings

Phase	2-Phase
-------	---------

Logistics

Standard Package	1
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com