



# 15° 4-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 48" 2-Phase

by CHANCE Utility  
Catalog ID: 2SBM48CLCL

48" Medium Duty Fiberglass 15° 4-Hole Cloverleaf Two-Phase Cutout /  
Arrester Standoff Bracket



\* Representative image

## Product Details

### General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	500 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359408147

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> <li>• 5.00 in</li> <li>• 6.00 in</li> <li>• 8.00 in</li> </ul>
Weight	14.1 lb

### Electrical Ratings

Phase	2-Phase
-------	---------

### Logistics

Pallet Quantity	30 EA
Standard Package	1

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)