
B74



MC CABLE DOUBLE BITE SADDLE CONNECTORS

90° Double Bite Saddle Connectors Steel/Malleable Iron





Catalog #: 3203DB

APPLICATIONS

Use 3/8 in. to 1 in. RACO Double Bite Saddle connectors in dry locations to connect flexible metal conduit, MCI, MCI-A, and AC cable to a box or enclosure Use 1-1/4 in. to 4 in. in dry locations to connect flexible metal conduit to a box or enclosure

PRODUCT FEATURES

Straight connectors have all steel construction that ensures mechanical protection for raceways

Straight connectors are available in 3/8 in. to 4 in. trade sizes 90 degree connectors have malleable iron and steel construction for added strength

90 degree connectors are available in 3/8 in. to 1 in. trade sizes

Dual saddle clamp ensures proper conduit and cable connection for raceway Zinc plated for corrosion protection

Tri-head screw/clamp design - connectors can be installed by using a slotted, Phillips, or Robertson head screwdriver Insulated throats on all Double Bite connectors provide maximum wire protection

UL LISTED

Standard 514B, File E195970 Standard 514B, File E195971

NEMA

NEMA FB-5

NEMA FB-6

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.

DRAWING DIMENSIONS

Dimension A: 2-1/2 in. Dimension B 2-1/2 in. Dimension C: 1-3/8 in.

PACKAGING

Package Type: Carton Ship Carton Qty.: Product UPC-A Labeled: 10 No 37.50 11.00 Weight (Lbs. Per/C): Ship Carton Length (in.): Ship Carton Width (in.): 2.80 Ship Carton Height (in.): Ctn Weight (Lbs.): 3.50 3.75

UPC Number: 050169532034 12of5: 50050169532039

Page 1 / 1