
B63



FLEXIBLE METAL 90 DEGREE SQUEEZE CONNECTORS

90° Squeeze Connectors Malleable Iron N/A



Catalog #: 3210

APPLICATIONS

For use in dry locations to bond flexible metal conduit to a box or enclosure

PRODUCT FEATURES

All malleable iron construction insures mechanical protection for the raceway

Electro zinc plated for added corrosion protection
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

CULUS

UL Listed E195969

GENERAL PRODUCT INFORMATION

Sub Class: Insulated Trade Size: 2-1/2 in.

DRAWING DIMENSIONS

Dimension A: 7-9/16 in. Dimension B: 1-7/64 in. 2-1/2 in. - 8 NPS 2.300 in. Thread Spec. B: Dimension C: 2.515 in. MAX 4-21/64 in. Dimension D: Dimension E:

PACKAGING

Package Type:
Ship Carton Qty.:
Product UPC-A Labeled:
Weight (Lbs. Per/C):
Ship Carton Length (in.): Carton Nο 365.20 4.81 Ship Carton Width (in.): Ship Carton Height (in.): 9.25 4.75 Ctn Weight (Lbs.): UPC Number:

3.65 050169032107 12of5: 50050169032102

Page 1 / 1