
B61

# FLEXIBLE METAL STRAIGHT SQUEEZE CONNECTORS

## Straight Squeeze Connectors, Insulated Malleable Iron

N/A

**A** 



Catalog #: 3304

#### APPLICATIONS

For use in dry locations to bond flexible metal conduit to a box or enclosure  $\ensuremath{\mathsf{N/\!A}}$ 

1 in.

1-11/16 in.

2-25/64 in.

33/64 in. 1 in. - 11-1/2 NPT .935 in. 1.364 - 1.408

#### PRODUCT FEATURES

All malleable iron construction insures mechanical protection for the raceway Electro zinc plated for added corrosion protection UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

#### CULUS

UL Listed E195969

GENERAL PRODUCT INFORMATION	
Trade Size:	

#### DRAWING DIMENSIONS

Dimension A: Dimension B: Thread Spec. B: Dimension C: Dimension D: Dimension E:

### PACKAGING

Package Type: Ship Carton Qty.: Product UPC-A Labeled: Weight (Lbs. Per/C): Ship Carton Length (in.): Ship Carton Height (in.): Ship Carton Height (in.): Ctn Weight (Lbs.): UPC Number: I2of5: Carton 25 No 28.50 10.00 5.25 4.31 7.13 050169033043 50050169033048