



**90 DEGREE CONDUIT AND CORD CONNECTORS - DIE CAST ZINC**

90 Degree Connectors Die Cast Zinc  
N/A

**B49.1**



Catalog #: 3422DC

**APPLICATIONS**

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit  
Use to positively bond the conduit to a box or enclosure

**PRODUCT FEATURES**

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
N/A

**CULUS**

Conduit Fittings 3HNN

**GENERAL PRODUCT INFORMATION**

Sub Class: Uninsulated  
Trade Size: 1/2 in.

**DRAWING DIMENSIONS**

Dimension A: -  
Thread Spec. A: -  
Dimension B: -  
Thread Spec. B: -  
Dimension C: -  
Thread Spec. C: -  
Dimension C A/C: -  
Dimension C A/F: -  
Dimension D: -  
Thread Spec. D: -  
Dimension E: -  
Thread Spec. E: -  
Dimension F: -

**PACKAGING**

Package Type: Carton  
Std. Pkg.: 25  
Ship Carton Qty.: 100  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 16.30  
Ship Carton Length (in.): 17.32  
Ship Carton Width (in.): 6.30  
Ship Carton Height (in.): 6.50  
Ctn Weight (Lbs.): 16.31  
UPC Number: 050169980125  
I2of5: 50050169980120