


# STRAIGHT CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON

Straight Connectors Steel/Malleable Iron

B47





Catalog #: 3522

#### APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit Use to positively bond the conduit to a box or enclosure

#### PRODUCT FEATURES

RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts All components are reusable - RACO liquid

Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening

Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation

All steel/iron components are zinc electro plated for added corrosion protection

3/8 in. to 1 in. Steel bodies, 1-1/4 in. to 4 in. Malleable iron bodies 3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts

N/A

UL LISTED

Standard 514B, UL Listed E195969

## CSA

C22.2 No. 18

# GENERAL PRODUCT INFORMATION

Sub Class: Insulated Trade Size: 3 in.

## DRAWING DIMENSIONS

Dimension A: 3-3/8 in. 1-3/64 in Dimension B Thread Spec. B: 3 in. - 8 NPT

#### PACKAGING

Package Type: Carton Ship Carton Qty.: Product UPC-A Labeled: No Weight (Lbs. Per/C): 361.60 Ship Carton Length (in.): Ship Carton Width (in.): 5.06 4.75 Ship Carton Height (in.): Ctn Weight (Lbs.): 5.19 3.62

UPC Number: 050169035221 30050169035222 12of5: