


**STRAIGHT GROUNDING CONDUIT AND CORD CONNECTORS****Straight Insulated Connector with Ground Lug, Steel/Malleable Iron
N/A****B50**

Catalog #: 3524-3

APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit, when installation of a copper or aluminum external bonding jumper is required RACO grounding liquidtight connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
 All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service
 Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
 Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground
 All metallic components are zinc electro plated for added corrosion protection
 3/8 in. to 1 in. Steel bodies; 1-1/4 in. to 4 in. Malleable Iron bodies
 3/8 in. to 1 in. Steel nuts; 1-1/4 in. to 4 in. Malleable Iron nuts
 N/A

UL LISTED

Standard 514B, UL Listed E195969

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size: 3-1/2 in.
 Min. Grounding Wire Capacity: #6 STR.
 Max Grounding Wire Capacity: #250 MCM

DRAWING DIMENSIONS

Dimension A: 3-31/32 in.
 Dimension B: 1-1/8 in.
 Thread Spec. B: 3-1/2 in. - 8 NPT
 Dimension C: 3-5/8 in.
 Dimension D: 1-13/16 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 1
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 524.00
 Ship Carton Length (in.): 6.50
 Ship Carton Width (in.): 6.50
 Ship Carton Height (in.): 5.13
 Ctn Weight (Lbs.): 5.24
 UPC Number: 050169352434
 I2of5: 50050169352439