
B58



90 DEGREE STRAIN RELIEF CONDUIT AND CORD CONNECTORS

90° Strain Relief Cord Connectors Steel/Malleable Iron



Catalog #: 3792-1

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

All steel/malleable construction provides mechanical strength

Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal Washers have cable size range imprinted for identification - eliminates misidentifying inventory

Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel

All metallic components are zinc electro plated for added corrosion protection Malleable iron bodies, Steel nuts

N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size: .125 - .250 1 Cable Range: Form Size:

DRAWING DIMENSIONS

1-3/64 in. Dimension A: 1/2 in. - 14 NPT 35/64 in. Thread Spec. A: Dimension B: 1-3/8 in. Dimension C: Dimension D: 1-7/16 in

PACKAGING

Package Type: Carton Ship Carton Qty.: Product UPC-A Labeled: 25 No Weight (Lbs. Per/C): Ship Carton Length (in.): 22.30 8.25 Ship Carton Width (in.): Ship Carton Height (in.): 5.00 4.00 Ctn Weight (Lbs.): 5.58

UPC Number: 12of5: 050169379219 50050169379214

Page 1 / 1