


**90 DEGREE STRAIN RELIEF CONDUIT AND CORD CONNECTORS****90° Strain Relief Cord Connectors Steel/Malleable Iron**
N/A**B58**

Catalog #: 3793-1

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
 RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

All steel/malleable construction provides mechanical strength
 Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened for a positive liquidtight seal
 Washers have cable size range imprinted for identification - eliminates misidentifying inventory
 Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
 All metallic components are zinc electro plated for added corrosion protection
 Malleable iron bodies, Steel nuts
 N/A

CULUS

UL File E195973

GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.
 Cable Range: .250 - .375
 Form Size: 3

DRAWING DIMENSIONS

Dimension A: 1-13/32 in.
 Thread Spec. A: 3/4 in. - 14 NPT
 Dimension B: 37/64 in.
 Dimension C: 1-5/8 in.
 Dimension D: 1-7/8 in.

PACKAGING

Package Type: Carton
 Ship Carton Qty.: 10
 Product UPC-A Labeled: No
 Weight (Lbs. Per/C): 31.50
 Ship Carton Length (in.): 6.25
 Ship Carton Width (in.): 4.50
 Ship Carton Height (in.): 4.25
 Ctn Weight (Lbs.): 3.15
 UPC Number: 050169379318
 I2of5: 50050169379313