




## COLOR-CODED 90° STRAIN RELIEF CONDUIT AND CORD CONNECTORS

Color-Coded 90° Strain Relief Cord Connectors Malleable Iron  
N/A

B58.2



Table					
RACO NO	TRADE SIZE	COLOR CODE	CABLE RANGE	DIM A	DIM B
3794-0	1/2"	RED	150-200	2.75	1.25
3794-1	1/2"	WHITE	200-300	2.75	1.25
3794-2	1/2"	BLUE	300-400	2.75	1.25
3794-3	1/2"	GREEN	400-500	2.75	1.25
3794-4	1/2"	BROWN	500-600	2.75	1.25
3795-0	3/4"	RED	150-200	3.25	1.44
3795-1	3/4"	WHITE	200-300	3.25	1.44
3795-2	3/4"	BLUE	300-400	3.25	1.44
3795-3	3/4"	GREEN	400-500	3.25	1.44
3795-4	3/4"	BROWN	500-600	3.25	1.44
3796-0	1"	RED	150-200	3.75	1.44
3796-1	1"	WHITE	200-300	3.75	1.44
3796-2	1"	BLUE	300-400	3.75	1.44
3796-3	1"	GREEN	400-500	3.75	1.44
3796-4	1"	BROWN	500-600	3.75	1.44
3797-0	1"	PURPLE	150-200	3.25	1.44
3798-0	1"	GREEN	200-300	3.75	1.75
3798-1	1"	YELLOW	300-400	3.75	1.75
3798-2	1"	PURPLE	400-500	3.88	1.75
3798-3	1"	GRAY	500-600	3.88	1.75
3798-4	1"	BLACK	600-1000	3.88	1.75



Catalog #: 3795-3

### APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable  
RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

### PRODUCT FEATURES

- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Malleable Iron construction provides mechanical strength and durability
- Metallic components are zinc plated for corrosion protection
- Unique Neoprene grommet design - grommet is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation
- Male tapered thread NPT
- Use RACO locknuts and sealing washers to complete a liquidtight installation on a sheet metal box or panel
- N/A

### CULUS

UL File E195973

### NEMA

NEMA 4

### GENERAL PRODUCT INFORMATION

Trade Size: 3/4 in.  
 Cable Range: .45 - .56  
 Color Code: Green

### DRAWING DIMENSIONS

Dimension A: 3.25  
 Dimension B: 1.44

### PACKAGING

Package Type: Carton  
 Ship Carton Qty.: 10  
 Product UPC-A Labeled: No  
 Weight (Lbs. Per/C): 45.30  
 Ship Carton Length (in.): 6.00  
 Ship Carton Width (in.): 6.00  
 Ship Carton Height (in.): 6.00  
 Ctn Weight (Lbs.): 4.53  
 UPC Number: 050169983324  
 I2of5: 50050169983329