



15° 2-Position Cutout / Arrester Standoff Bracket, 36" 13" Three-Phase w/ Hardware

by CHANCE Utility
Catalog ID: 3SBM3613AMTB

36 13 Medium Duty 15° 2-Position Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware



* Representative image

Product Details

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1200 lb
UPC	096359451891

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	13 in
Length	36.00 in
Mounting Bolt Spacing	6.00 in 8.00 in
Weight	20.1 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Pallet Quantity	5 EA
Standard Package	5

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com