



15° 4-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 36" 13" 3-Phase w/ Hardware

by CHANCE Utility
Catalog ID: 3SBM3613CLH

36" 13" Medium Duty Fiberglass 15° 4-Hole Cloverleaf Three-Phase Cutout
/ Arrester Standoff Bracket w/ Hardware



* Representative image

Product Details

General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1,200 lb
UPC	096359501657

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	13 in
Length	36.00 in
Mounting Bolt Spacing	• 6.00 in • 8.00 in
Weight	20.0 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Standard Package	5
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com