



# 15° 4-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 36" 13" 3-Phase

by CHANCE Utility  
Catalog ID: 3SBM3613CL

36" 13" Medium Duty Fiberglass 15° 4-Hole Cloverleaf Three-Phase Cutout / Arrester Standoff Bracket



\* Representative image

## Product Details

### General

Description - End Fitting	3 Position Cloverleaf Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	1,200 lb
UPC	096359451006

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	36 in
Distance from Pole - Third Phase	13 in
Length	36.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> <li>• 6.00 in</li> <li>• 8.00 in</li> </ul>
Weight	20.0 lb

### Electrical Ratings

Phase	3-Phase
-------	---------

### Logistics

Standard Package	5
------------------	---

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)