



# 0° 2-Position Cutout / Arrester Standoff Bracket (No Hardware), 48" 13" Three-Phase

by CHANCE Utility  
Catalog ID: 3SBM4813CT

48" 13" Medium Duty Fiberglass 0° 2-Position Three-Phase Cutout / Arrester Standoff Bracket (No Hardware)



\* Representative image

## Product Details

### General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359451884

### Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	13 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"><li>• 6.00 in</li><li>• 8.00 in</li></ul>
Weight	23.0 lb

### Electrical Ratings

Phase	3-Phase
-------	---------

### Logistics

Carton Quantity	5 EA
Standard Package	5

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)