



0° 1-Position Cutout / Arrester Standoff Bracket w/ Hardware (No Collars), 48" 18" 3-Phase

by CHANCE Utility
Catalog ID: 3SBM4818SGLB

48" 18" Medium Duty Fiberglass 0° 1-Position Cutout / Arrester 3-Phase Standoff Bracket w/ Hardware (No Collars)



* Representative image

Product Details

General

| | |
|--|----------------------------|
| Description - End Fitting | 1 Position Apparatus Mount |
| Strength Rating - Minimum Ultimate, Longitudinal (L) | 700 lb |
| Strength Rating - Minimum Ultimate, Transverse (T) | 5000 lb |
| Strength Rating - Minimum Ultimate, Vertical (V) | 900 lb |
| UPC | 096359522164 |

Dimensions

| | |
|----------------------------------|---|
| Diameter - Rod / Tube | 1.5 in |
| Distance From Pole | 48 in |
| Distance from Pole - Third Phase | 18 in |
| Length | 48.00 in |
| Mounting Bolt Spacing | <ul style="list-style-type: none">• 6.00 in• 8.00 in |
| Weight | 14.1 lb |

Electrical Ratings

| | |
|-------|---------|
| Phase | 3-Phase |
|-------|---------|

Logistics

| | |
|------------------|---|
| Standard Package | 5 |
|------------------|---|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com