



15° 1-Position Cutout / Arrester Standoff Bracket, 48" 24" Three-Phase w/Hardware (No Collars)

by CHANCE Utility
Catalog ID: 3SBM4824AMB

48" 24" Medium Duty Fiberglass 15° 1-Position Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware (No Collars)



* Representative image

Product Details

General

Description - End Fitting	1 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	1500 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359396451

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	24 in
Length	48.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none"> • 6.00 in • 8.00 in
Weight	15.7 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Standard Package	5
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com