



15° 2-Position Cutout / Arrester Standoff Bracket, 48" 24" Three-Phase w/ Hardware

by CHANCE Utility
Catalog ID: 3SBM4824AMTB

48 24 Medium Duty 15° 2-Position Three-Phase Cutout / Arrester Standoff Bracket w/ Hardware



* Representative image

Product Details

General

Description - End Fitting	2 Position Apparatus Mount
Strength Rating - Minimum Ultimate, Longitudinal (L)	700 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359396475

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	24 in
Length	48.00 in
Mounting Bolt Spacing	6.00 in 8.00 in
Weight	23.3 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Carton Quantity	5 EA
Standard Package	5

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com