



15° 7-Hole Cloverleaf Cutout / Arrester Standoff Bracket, 48" 24" Three-Phase

by CHANCE Utility
Catalog ID: 3SBM4824DFCL

48" 24" Medium Duty 15° 7-Hole Cloverleaf Three-Phase Cutout / Arrester Standoff Bracket



Product Details

General

Description - End Fitting	7-Hole Cloverleaf
Strength Rating - Minimum Ultimate, Longitudinal (L)	800 lb
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	900 lb
UPC	096359475200

Dimensions

Diameter - Rod / Tube	1.5 in
Distance From Pole	48 in
Distance from Pole - Third Phase	18 in
Mounting Bolt Spacing	6.00 in - 8.00 in
Radius - FWDE Wrap-Around	1.5
Weight	17.30 lb

Electrical Ratings

Phase	3-Phase
-------	---------

Logistics

Standard Package	5
------------------	---

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com