



*Commercial, Industrial
and Residential Electrical Products*

3/8 in. Armored Cable Connector, .470- .610

Catalog #:
40RAC



40RAC	
CABLE TYPE (Steel & Aluminum)	CABLE RANGES
MC	14/3 - 10/3
MCI-A	
AC	
AC HCF	14/2 - 10/3
MCI-A HCF	12/2 - 10/3
MC-PCS (SOLID)	12/2 - 12/3
RWFMC CONDUIT	3/8" TRADE SIZE FLEX Anti Short Bushing Required

Cable Diameter Range: 0.470" - 0.610"

FEATURE BENEFIT

Push-In MC Cable connector makes it easy to terminate flexible metal clad cable or any standard electrical box

PRODUCT FEATURES

- Fits standard 1/2 In. knockouts in electrical boxes or enclosures
- Designed to terminate MC-PCS, MCI, MCI-A, AC, HCF, and FMC
- 40RAC tinted blue inside to indicate larger cable range, suitable for MC-PCS in smart buildings
- Die-cast zinc construction with nylon anti-short bushing
- For use in dry locations
- Includes pre-assembled anti-short bushing

APPLICATIONS

RACO's new Push-in cable connectors make it easy to secure metal-clad cable into boxes or enclosures. Simply insert a cable into the cable opening, then snap the box end of the connector into a box knockout, done! No tools needed for a secure assembly. Push-in connectors are perfect for new or old work and can be removed and reused.

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169000403
Ea Length/Depth (in.):	1.471
Ea Width (in.):	0.948
Ea Height (in.):	0.992
Wt. Ea. (Lbs.):	0.071
Package Type:	Loose
Product UPC-A Labeled:	No

PACKAGING

Case I2of5:	50050169000408
Pack I2of5:	30050169000404
Standard Carton Qty:	500
Pack Carton Qty:	50
Min Order Qty:	50

Revision 1, September 2019



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

