


3 IN. X 2 IN. SWITCH BOXES - 1-1/2 TO 2-1/2 IN. DEEP WITH CONDUIT KO'S

2 in. Deep Switch Box - Gangable with Conduit KO's Plaster Ears

A47





Catalog #: 420

APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets

PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices

Plaster ears allow a box to be used in "old work" applications

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Conduit Wiring System:

CONFIGURATION End Knockouts:

(2) 1/2 in. Ends Cable: No Bracket Bracket Type: Side Knockout(s): (4) 1/2 in. Bottom Knockouts(s) (2) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2 in.

PRODUCT MEASUREMENTS

2 in. 10.3 (168.8) Depth: Cubic Inches (cm3): Wt. Ea. (Lbs.): 0.464 Product Length (in.): Product Width (in.): 2.00 4.22 Product Height (in.): 2.00

PACKAGING

Minimum Pack Qty.: Std. Pkg.: Product UPC-A Labeled: 25 25 Yes Weight (Lbs. Per/C): Ship Carton Length (in.): 46.40 12.88 Ship Carton Width (in.): 5.63 8.75 11.60 Ship Carton Height (in.): Ctn Weight (Lbs.): Pallet Qty: UPC Number: 3600 050169004203 12of5: 40050169004201

Page 1 / 1