




STRAIN RELIEF CONDUIT AND CORD CONNECTORS - ALUMINUM

Straight Strain Relief Cord Connectors Aluminum
N/A

B60



Catalog #: 4803-4

APPLICATIONS

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable
Aluminum liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations

PRODUCT FEATURES

- Aluminum construction provides a corrosion resistant installation
- Patented Gotcha® ring incorporates a split hinge design to prevent friction and to provide strain relief
- Neoprene grommet
- Knurled compression nut allows the fittings to be hand tightened to UL requirements
- Gotcha® ring is color-coded for sizing identification
- N/A

UL LISTED

Standard 514B

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Trade Size:	3/4 in.
Cable Range:	.375 - .500
Color Code:	Blue
Form Size:	2

DRAWING DIMENSIONS

Dimension A:	1.13 in.
Dimension B:	.55 in.
Dimension C:	1.10 in.
Dimension D:	.64 in.
Dimension E:	A/C 1.29 in., A/F 1.13 in.

PACKAGING

Package Type:	Carton
Ship Carton Qty.:	25
Product UPC-A Labeled:	No
Weight (Lbs. Per/C):	12.10
Ship Carton Length (in.):	8.75
Ship Carton Width (in.):	5.00
Ship Carton Height (in.):	4.00
Ctn Weight (Lbs.):	3.03
UPC Number:	050169480342
I2of5:	50050169480347