



BOLT, THIMBLEYE, ANGLE, 3/4in x 10in

by CHANCE Utility
Catalog ID: 5110T

Angled thimbleye bolt, 3/4" diameter x 10" length, with 4" thread length and cone pointed end. Includes one square nut. Internal eye dimensions are 11/16" x 13/16". Rated tensile strength is 18,350 lbs. Hot dip galvanized per ASTM A-153. RUS listed, ao - Bolt, strand eye, straight (thimble eye).



* Representative image

Product Details

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb
Type	Thimbleye Bolts
UPC	096359072270

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	10.00 in
Length - Threaded Area	4
Weight	2.23 lb

Certifications and Compliance

RUS Listed Reference	ba - Bolt, angle eye (thimble eye)
----------------------	------------------------------------

Logistics

Pallet Quantity	960 EA
-----------------	--------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com