




ROUND & RECTANGULAR CLUSTER COVERS

4in. Round Cluster Cover - One Threaded Outlet

D22



Catalog #: 5193-1

APPLICATIONS

For use with BELL® single gang or round weatherproof boxes
Cluster covers provide an easy means of mounting BELL® lampholders and other accessories.

PRODUCT FEATURES

Rugged die cast construction
State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
Includes gasket and mounting hardware
Multi-lingual instructions in each package
Three hole covers supplied with two closure plugs

UL LISTED

Standard 514A

CULUS

N/A

CSA

C22.2 No. 18

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

Color: White

CONFIGURATION

Number Of Outlets: 1

PRODUCT MEASUREMENTS

Outlet Size: 1/2 in.
Wt. Ea. (Lbs.): 0.150

PACKAGING

Package Type: Shrink
Std. Pkg.: 20
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 15.00
Ship Carton Length (in.): 13.19
Ship Carton Width (in.): 4.25
Ship Carton Height (in.): 8.50
Ctn Weight (Lbs.): 6.46
Pallet Qty: 3000.00
UPC Number: 050169519318
I2of5: 50050169519313