

2-5/8 In. Deep Two Gang Box

Catalog #:
5388-0



FEATURE BENEFIT

Provides five 3/4 inch Threaded Outlets and multi-lingual instructions in each package

PRODUCT FEATURES

- Rugged die-cast aluminum construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Includes two 3/4 in. closure plugs, gasket and mounting hardware
- Internal hub threads comply with NEMA requirements and will accept all threaded fittings and threaded conduit
- Ground screw installed

APPLICATIONS

For use in branch circuit wiring in wet, damp, or dry locations

May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

CERTIFICATIONS



NEMA 3R Rated

PRODUCT SPECIFICATIONS

UPC Number:	050169538807
Ea Length/Depth (in.):	2.625
Ea Width (in.):	4.50
Ea Height (in.):	4.50
Wt. Ea. (Lbs.):	1.261
Color:	Gray
Gangs:	2
Package Type:	Shrink
Package Contents:	1
Product UPC-A Labeled:	Yes

SHIPPING

I2of5:	50050169538802
Standard Carton Qty:	9
Min Order Qty:	1
Ship Carton Length (in.):	16.188
Ship Carton Width (in.):	6.50
Ship Carton Height (in.):	8.50
Ship Carton Weight (Lbs.):	11.350
Pallet Qty:	648

Revision 1, July 2018



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

BELL
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/bell/en

