
## 3 IN. X 2 IN. SWITCH BOXES - 1-1/2 TO 2-1/2 IN. DEEP WITH NONMETALLIC SHEATHED CABLE CLAMPS

2-1/2 in. Deep Switch Boxes - Gangable with Nonmetallic Sheathed Cable Clamps Plaster Ears, Old Work, 3/4 in. Sheet Rock Max.

A50



Catalog #: 545

#### APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets

### PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices

Plaster ears allow a box to be used in "old work" applications

### UL LISTED

File E195978

#### COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

# FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

## GENERAL PRODUCT INFORMATION

Nonmetallic Sheathed Cable Wiring System:

Country of Origin: USA

# CONFIGURATION

End Knockouts: (2) 1/2 in Ends Cable: Bracket Type: No Bracket Side Knockout(s): Bottom Knockouts(s):

DRAWING DIMENSIONS

2-1/2 in. Dimension A:

## PRODUCT MEASUREMENTS

2-1/2 in Depth: Cubic Inches (cm3): 12.5 (204.8) Wt. Ea. (Lbs.): Product Length (in.): 0.650 2.50 Product Width (in.): 4.22 3.41 Product Height (in.):

**PACKAGING** 

Minimum Pack Qty.: 20 Std. Pkg.: 20 Product UPC-A Labeled: Weight (Lbs. Per/C): Yes 65.00 Ship Carton Length (in.): 13.00 Ship Carton Width (in.): 6.13 Ship Carton Height (in.): 10.75 Ctn Weight (Lbs.): Pallet Qty: 13.00 1820

UPC Number: 050169005453 50050169005458 12of5

Page 1 / 1