
LAMPHOLDER / COVER COMBOS

4in. Round Cover Combinations for 75-150 Watt Par 38 Lamps (1) Lampholder / (1) Cover

D25





Catalog #: 5624-6

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations For use with BELL® single gang or round weatherproof boxes

PRODUCT FEATURES

Rugged die cast construction
State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
Includes gasket and mounting hardware
Multi-lingual instructions in each package
No Need to purchase separate components
N/A

UL LISTED

File E225082

CSA

C22.2 No. 18

GENERAL PRODUCT INFORMATION

Color: White

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.840

PACKAGING

 KCKAGING
 Carded

 Package Type:
 4

 Std. Pkg.:
 4

 Product UPC-A Labeled:
 Yes

 Weight (Lbs. Per/C):
 84.00

 Ship Carton Length (in.):
 14.19

 Ship Carton Width (in.):
 6.69

 Ship Carton Height (in.):
 5.50

 Ctn Weight (Lbs.):
 3.36

 Pallet Qty:
 640.00

 UPC Number:
 050169562468

 I2of5:
 50050169562463