



LAMPHOLDER / COVER & BOX COMBO

Single Gang Light Kits for 75-150 Watt Par 38 Lamps
Box, Cover, Photocell & (2) Lampholders

D26



Catalog #: 5883-6

APPLICATIONS

For general outdoor lighting in wet, damp or dry locations
N/A

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components

UL LISTED

Listed

GENERAL PRODUCT INFORMATION

Color: White

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 1.823

PACKAGING

Package Type:	Boxed
Std. Pkg.:	4
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	182.30
Ship Carton Length (in.):	10.81
Ship Carton Width (in.):	6.25
Ship Carton Height (in.):	8.81
Ctn Weight (Lbs.):	7.29
Pallet Qty:	448.00
UPC Number:	050169588369
I2of5:	50050169588364