




TIER GARDEN LIGHTS

**3-Tier Garden Light
Incandescent 40W Max**

D27



Catalog #: 5884-8

APPLICATIONS

For accent lighting along walkways, driveways, terraces, porches and garden areas
N/A

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes screw-in clear glass globe
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package

CULUS

Listed

GENERAL PRODUCT INFORMATION

Color: Green

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 3.050

PACKAGING

Package Type: Boxed
 Std. Pkg.: 2
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 305.00
 Ship Carton Length (in.): 10.81
 Ship Carton Width (in.): 6.25
 Ship Carton Height (in.): 8.81
 Ctn Weight (Lbs.): 6.10
 Pallet Qty: 168.00
 UPC Number: 050169588482
 I2of5: 50050169588487