




SINGLE GANG RECTANGULAR FLOOR BOXES - CONCRETE POUR

Single-Gang Fully Adjustable Floor Box, Cast Iron
N/A

A98



Catalog #: 6262

APPLICATIONS

RACO® rectangular series floor boxes are ideally suited for heavy floor traffic applications, such as malls, department stores, banks and schools
Floor boxes are installed in poured concrete floors and are fed with conduit
RACO® floor boxes are used in branch circuit wiring

PRODUCT FEATURES

- Cast iron, water-tight body, fully adjustable
- Gray powder coat paint inside and out for additional corrosion resistance
- 3/4" threaded conduit openings are standard
- Brass tile flange provided with box
- RACO® 6292 or 6295 carpet flange must be ordered separately
- RACO® 6250, 6288, 6289, or 6291 brass cover must be ordered separately
- Interior and exterior leveling screws permit adjustment to meet finished floor
- Disposable concrete cap to prevent the entry of concrete during pour included
- N/A

UL LISTED

File E195978

GENERAL PRODUCT INFORMATION

Wiring System: Conduit

CONFIGURATION

Number Of Outlets: 4
Bottom Knockouts(s): ---

PRODUCT MEASUREMENTS

Outlet Size:	3/4 in.
Cubic Inches (cm3):	33.0 (540.7)
Wt. Ea. (Lbs.):	4.280
Product Length (in.):	4.69
Product Width (in.):	3.15
Product Height (in.):	4.69

PACKAGING

Minimum Pack Qty.:	4
Std. Pkg.:	4
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	428.00
Ship Carton Length (in.):	12.37
Ship Carton Width (in.):	6.12
Ship Carton Height (in.):	9.00
Ctn Weight (Lbs.):	17.12
Pallet Qty:	420
UPC Number:	050169062623
I2of5:	50050169062628