



* Representative image

Anchor, Tool, Kelly Bar Adapter, 2.625in Hex, 10,000 ft-lb rating

by CHANCE Utility
Catalog ID: 630012HD

Standard Kelly Bar Adapter 10,000 Ft Lbs (13,558 N-M) for 2 5/8" (66.7 mm) Hex Kelly Bar.

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Locking Dog Assembly has six holes for 1/2" bolts on a 5-1/4" bolt circle, comes with six 1/2" Grade 5 bolts, nuts and lock washers
- Painted with green paint

Product Details

General

| | |
|----------------------|--------------------------------|
| Bolt Grade | 5 |
| Kelly Bar Shape | Hex |
| Number of Bolt Holes | 6 |
| Torque Rating | 10000 ft-lbs |
| Type | Anchor/Pile Installation Tools |
| UPC | 096359227434 |

Dimensions

| | |
|-----------------------------------|-----------|
| Anchor Installation Hole Size | 0.5 in |
| Diameter - Bolt | 0.5 in |
| Diameter - Bolt Circle | 5.25 in |
| Kelly Bar Adapter Inside Width | 2.625 in |
| Kelly Bar Hole Distance to Flange | 4.25 in |
| Length | 8.125 in |
| Weight | 17.640 lb |

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 60 EA |
| Standard Package | 1 |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com