4 in. Square Two Device Switch Boxes, 2-1/8 in. Deep - Drawn with Conduit KO's



Catalog# 680

APPLICATIONS

Installers can save time and cut installation costs with two gang switch boxes

Larger capacity boxes are ideal for today's designs where there is a need to install two devices at one location

Drawn boxes are ideal for exposed work applications (surface mounted wiring)

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Wiring System: Condu

CONFIGURATION

Bracket Type: No Bracket
Drawn or Welded: Drawn
Raised Ground: No
Side Knockout(s): (12) 1/2 in.
Bottom Knockouts(s): (5) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-1/8 in.
Dimension B: 4 in.
Dimension C: 4 in.

PRODUCT MEASUREMENTS

 Depth:
 2-1/8 in.

 Cubic Inches (cm3):
 30.3 (496.5)

 Wt. Ea. (Lbs.):
 0.796

 Product Length (in.):
 2.19

 Product Width (in.):
 4.00

 Product Height (in.):
 4.00

PACKAGING

 Minimum Pack Qty.:
 25

 Std. Pkg.:
 25

 Product UPC-A Labeled:
 Yes

 Weight (Lbs. Per/C):
 79.60

 Ship Carton Length (in.):
 18.75

 Ship Carton Width (in.):
 8.88

 Ship Carton Height (in.):
 7.38

 Ctn Weight (Lbs.):
 19.90

 Pallet Qty:
 1750

 LINCA Methods:
 19.90

UPC Number: 050169006801 I2of5: 50050169006806