



**MASONRY BOXES & SUPPORTS**

**Block-Loc Masonry Boxes, 3-1/2" Deep - Nongangable with Conduit KO's  
1 Gang, Welded**

**A59**



Catalog #: 695B

**APPLICATIONS**

For power and data outlets in masonry block walls  
Secures masonry box in block wall and prevents box from moving during construction

**PRODUCT FEATURES**

Integral brackets securely hold box to concrete block from front and back in masonry block walls, even in irregular openings  
Quick and accurate positioning  
Break off front tabs

**UL LISTED**

File E195978

**CULUS**

N/A

**COMPLIANCES**

They are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at [www.ul.com](http://www.ul.com)

**FIRE RESISTANCE**

Acceptable for use in 2-hour rated walls

**GENERAL PRODUCT INFORMATION**

Wiring System: Conduit  
Color: Gray

**CONFIGURATION**

End Knockouts: (4) 1/2" - 3/4" Conc. KO  
Drawn or Welded: Welded  
Raised Ground: No  
Gangs: 1  
Side Knockout(s): (4) 1/2" - 3/4" Conc. KO  
Bottom Knockouts(s): (2) 1/2" - 3/4" Conc. KO

**PRODUCT MEASUREMENTS**

Depth: 3-1/2 in.  
Cubic Inches (cm3): 22.5  
Wt. Ea. (Lbs.): 0.946  
Product Length (in.): 3.500  
Product Width (in.): 3.547  
Product Height (in.): 3.797

**PACKAGING**

Package Type: Boxed  
Minimum Pack Qty.: 18  
Std. Pkg.: 18  
Ship Carton Qty.: 18  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 94.605  
Ship Carton Length (in.): 11.125  
Ship Carton Width (in.): 10.000  
Ship Carton Height (in.): 8.500  
Ctn Weight (Lbs.): 17.029  
Pallet Qty: 1440  
UPC Number: 050169500620  
I2of5: 50050169500625