



**Commercial, Industrial
and Residential Electrical Products**

3-Gang Masonry Box, Nongangable, 3-1/2 In. Deep, Nineteen Concentric KO's

Catalog #:
697



FEATURE BENEFIT

Rugged electrical multi-gang box designed for use in masonry applications

PRODUCT FEATURES

- Rugged welded design does not fall apart during construction
- Available from one to six gang configurations in both 2-1/2 In. and 3-1/2 In. depths
- Rectangular shape fits square cuts in block
- Large volume design allows for additional work room inside the box
- Standard 1/2 In. and 3/4 In. concentric knockouts
- Device ears inside the box prevent mortar from getting in the device holes
- Steel voltage partition #971 fits all 2-1/2 In. or 3-1/2 In. depths
- Standard wall plates can be used
- Supplied with nineteen (19) 1/2 & 3/4 In. concentric knockouts
- Welded steel construction
- Standard device spacing with tapped 6-32 holes for devices
- 67.3 Cu. In. capacity
- For 6, 8, and 10 In. block walls

APPLICATIONS

RACO® Masonry boxes are designed to accommodate the mounting of switches or other devices in masonry walls, 3-1/2 In. deep boxes are used in 6 In. or 8 In. block walls

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169006979
Ea Length/Depth (in.):	3.50
Ea Width (in.):	5.594
Ea Height (in.):	3.75
Wt. Ea. (Lbs.):	1.600
Package Type:	Loose
Product UPC-A Labeled:	No

SHIPPING

Case I2of5:	50050169006974
Standard Carton Qty:	10
Min Order Qty:	10

Revision 1, January 2020



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

