




**MASONRY BOXES & SUPPORTS**

**Block-Loc Masonry Boxes, 3-1/2" Deep - Nongangable with Conduit KO's  
3 Gang, Welded**

**A59**



Catalog #: 697B

**APPLICATIONS**

For power and data outlets in masonry block walls  
Secures masonry box in block wall and prevents box from moving during construction

**PRODUCT FEATURES**

Integral brackets securely hold box to concrete block from front and back in masonry block walls, even in irregular openings  
Quick and accurate positioning  
Break off front tabs

**UL LISTED**

File E195978

**CULUS**

N/A

**COMPLIANCES**

They are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at [www.ul.com](http://www.ul.com)

**FIRE RESISTANCE**

Acceptable for use in 2-hour rated walls

**GENERAL PRODUCT INFORMATION**

Wiring System: Conduit  
Color: Gray

**CONFIGURATION**

End Knockouts: (12) 1/2" - 3/4" Conc. KO  
Drawn or Welded: Welded  
Raised Ground: No  
Gangs: 3  
Side Knockout(s): (4) 1/2" - 3/4" Conc. KO  
Bottom Knockouts(s): (3) 1/2" - 3/4" Conc. KO

**PRODUCT MEASUREMENTS**

Depth: 3-1/2 in.  
Cubic Inches (cm3): 67.3  
Wt. Ea. (Lbs.): 1.704  
Product Length (in.): 3.578  
Product Width (in.): 7.172  
Product Height (in.): 3.797

**PACKAGING**

Package Type: Boxed  
Minimum Pack Qty.: 12  
Std. Pkg.: 12  
Ship Carton Qty.: 12  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 170.400  
Ship Carton Length (in.): 14.500  
Ship Carton Width (in.): 10.880  
Ship Carton Height (in.): 8.250  
Ctn Weight (Lbs.): 20.448  
Pallet Qty: 660  
UPC Number: 050169500644  
I2of5: 50050169500649