

# 6ABV-750

by CMC  
Catalog ID: 6ABV-750



General purpose transformer connectors, Dual-Rated for Aluminum or Copper Conductors

- Compact design relieves cantilever stress.
- Clear Plated for low contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Designed for installation on standard NEMA bolt holes.
- Fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Supplied with radial tipped set-screws.

## Product Details

### General

Material	Aluminum
Number of Holes	2
Type	ABV

### Dimensions

Dimensions	4.9 in x 3.75 in x 3 in
Height	3 in
Length	4.9 in
Width	3.75 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Conductor Range	750 Kcmil - #1/0 AWG
Number Of Conductors	6



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

