



\* Representative image

# BOLT, SPOOL, DOUBLE-UPSET, 5/8in x 8in

by CHANCE Utility  
Catalog ID: 7826

Double-upset spool bolt, 5/8" diameter x 8" shank length, with 6" thread length and cone pointed end. Overall length is 13 3/4". Pole offset distance is 1". Includes one square nut with cotter key. Rated cantilever load is 800 lbs. Hot dip galvanized per ASTM A-153. Manufactured in compliance with ANSI C135.31. RUS listed, q - Bolt, double upset.

## Product Details

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb
Type	Spool Bolts
UPC	096359074489

### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	8.00 in
Length - Threaded Area	6
Weight	1.63 lb

### Certifications and Compliance

RUS Listed Reference	q - Bolt, double upset
----------------------	------------------------

### Logistics

Pallet Quantity	1280 EA
-----------------	---------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)