
OLD WORK NON-METALLIC CABLE BOXES

Old Work Cable Boxes - For Nonmetallic Sheathed Cable Single-gang, 2-29/32 in. Deep, 14.0 Cu. in., Flush Mount

A78





Catalog #: 7887RAC

APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires Accommodates wiring devices such as switches and receptacles Provide excellent protection for wiring system or devices

PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install Self-clamping wire entry clamps

Extra long, metal swing arms ensure installation

UL LISTED

File E195963

COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book Federal Manufacturer's number 28488

FIRE RESISTANCE

2-hour fire rating, UL Orange Book

US PATENTS

4,183,486; 4,874,905; 4,580,689; 4,666,599

OTHER PATENTS

Canada 1,237,515; 1,260,599

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable

Color Gray

RECOMMENDED MAX LOAD Fixture (Static) Lbs.:

CONFIGURATION

Cable Clamps:

DRAWING DIMENSIONS

2-29/32 in. Dimension A Dimension C 2-1/4 in.

PRODUCT MEASUREMENTS

Depth: 2-29/32 in. Cubic Inches (cm3): 14.0 (229.4) Wt. Ea. (Lbs.): Product Length (in.): 0.190 2.91 4.13 2.25 Product Width (in.): Product Height (in.):

PACKAGING Minimum Pack Qty.: 50 Std. Pkg.: Product UPC-A Labeled: 50 Yes Weight (Lbs. Per/C): 19.00 Ship Carton Length (in.): Ship Carton Width (in.): 24.00 8.00

 Ship Carton Height (in.):
 16.00

 Ctn Weight (Lbs.):
 9.50

 Pallet Qty:
 1250

 UPC Number:
 050169978870

 I20f5:
 50050169978875