




ROUND NON-METALLIC CABLE BOXES

3-1/2 in. Round Ceiling Boxes - With Captive Nails for Nonmetallic Sheathed Cable
2-5/8 in. Deep, 18.0 Cu. in., 1/2 in. Setback, Nails, Ground Plate

A80



Catalog #: 7919RAC

APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires
Provide excellent protection for wiring system or devices
For use wherever lighting fixture canopies are to be installed - not designed for ceiling fan support

PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install
Self-clamping wire entry clamps
Round fixture boxes offer an optional front-mounted grounding screw
Oversized nail support that resists hammer impact and prevents box deformation

UL LISTED

File E 195963

COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book
Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book
Federal Manufacturer's number 28488

FIRE RESISTANCE

2-hour fire rating, UL Orange Book

US PATENTS

4,874,905; 4,605,816; 4,580,689; 4,666,055

OTHER PATENTS

Canada 1,233900; 1,237,515; 1,260,599

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable
Color: Gray

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No
Fixture (Static) Lbs.: 50

CONFIGURATION

Cable Clamps: 6

DRAWING DIMENSIONS

Dimension A: 2-5/8 in.

PRODUCT MEASUREMENTS

Depth: 2-5/8 in.
Cubic Inches (cm3): 18.0 (295.0)
Wt. Ea. (Lbs.): 0.204
Product Length (in.): 2.63
Product Width (in.): 5.50
Product Height (in.): 4.00

PACKAGING

Minimum Pack Qty.: 75
Std. Pkg.: 75
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 20.40
Ship Carton Length (in.): 24.00

Ship Carton Width (in.):	13.00
Ship Carton Height (in.):	16.00
Ctn Weight (Lbs.):	15.30
Pallet Qty:	1125
UPC Number:	050169979198
I2of5:	50050169979193