



**Commercial, Industrial
and Residential Electrical Products**

4 In. Square Box, Drawn, 1-1/2 In. Deep with Sixteen 1/2 In. KO's, Raised Ground

Catalog #:
8190



FEATURE BENEFIT

Shallow box for installation in walls or ceilings for light fixtures, switches or receptacles

PRODUCT FEATURES

- Ideal for exposed work applications
- Combination screw heads allow quick installation
- Drawn construction
- Sixteen 1/2 In. knockouts
- 21.0 Cu. In. capacity
- Raised ground, 10 In. #12 stranded copper pigtail
- Acceptable in 2-hour fire rated walls

APPLICATIONS

- Designed to enclose electrical wiring, switches, receptacles or lighting fixtures
- Constructed from 1/16 In. pre-galvanized steel
- 8-32 cover mounting screws assembled

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169001905
Ea Length/Depth (in.):	1.563
Ea Width (in.):	4.00
Ea Height (in.):	4.00
Wt. Ea. (Lbs.):	0.664
Package Type:	Loose
Product UPC-A Labeled:	Yes



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

PACKAGING

Case I2of5:	50050169001900
Standard Carton Qty:	50
Min Order Qty:	50

600V

Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, December 2019



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

