



Commercial, Industrial and Residential Electrical Products

4 In. Square Box, Welded, 2-1/8 In. Deep, Ten 1/2 In. KO's & Six TKO's, Raised Ground

Catalog #: 8232



FEATURE BENEFIT

Welded 4 In. square box for installing receptacles, switches or fixtures in walls or ceilings

PRODUCT FEATURES

- · Combination screw heads allow quick installation
- Welded construction
- Eight 1/2 In. knockouts and four TKO knockouts
- 30.3 Cu. In. capacity
- · Raised ground
- · Acceptable in 2-hour fire rated walls

APPLICATIONS

Square box is used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices inside walls or ceilings for lighting fixtures, switches or receptacles

CERTIFICATIONS



PRODUCT SPECIFICATIONS

 UPC Number:
 050169002322

 Ea Length/Depth (in.):
 2.434

 Ea Width (in.):
 4.00

 Ea Height (in.):
 4.00

 Wt. Ea. (Lbs.):
 0.884

 Package Type:
 Loose

 Product UPC-A Labeled:
 Yes

SHIPPING

Case I2of5: 50050169002327

Standard Carton Qty: 25 Min Order Qty: 25





All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com



Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts

Revision 1, February 2020



RACO 3902 W. Sample St. South Bend, IN 46619 574-234-7151 www.hubbell.com/raco/en

