




4 IN. OCTAGON DRAWN BOXES WITH ARMORED CABLE / METAL CLAD / FLEX CLAMPS

4 in. Octagon Box, 1-1/2 in. Deep - Drawn with Armored Cable/Metal Clad/Flex Clamps
Box with 14-1/4 in. to 22-1/2 in. Bar Hanger

A40



Catalog #: 8325

APPLICATIONS

RACO® Octagon Boxes are used in the installation of ceiling or wall lighting fixtures
N/A

PRODUCT FEATURES

Fixture bar hanger allows box to be located anywhere along length of bar

UL LISTED

File E195978

GENERAL PRODUCT INFORMATION

Wiring System: : Armored Cable/Metal Clad/MCI-A/Flex

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: No
Fixture (Static) Lbs.: 10*

CONFIGURATION

Cable Priouts: 4
Bracket Type: No Bracket
Drawn or Welded: Drawn
Raised Ground: No
Side Knockout(s): (2) 1/2 in.
Bottom Knockouts(s): ---

DRAWING DIMENSIONS

Dimension A: 1-1/2 in.
Dimension B: 4 in.

PRODUCT MEASUREMENTS

Depth: 1-1/2 in.
Cubic Inches (cm3): 15.5 (254.0)
Wt. Ea. (Lbs.): 0.924
Product Length (in.): 2.13
Product Width (in.): 3.56
Product Height (in.): 14.50

PACKAGING

Minimum Pack Qty.: 25
Std. Pkg.: 25
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 92.40
Ship Carton Length (in.): 16.13
Ship Carton Width (in.): 7.75
Ship Carton Height (in.): 11.25
Ctn Weight (Lbs.): 23.10
Pallet Qty: 1650
UPC Number: 050169003251
I2of5: 50050169003256