


3 IN. X 2 IN. SWITCH BOXES - 1-1/2 TO 2-1/2 IN. DEEP WITH CONDUIT KO'S

2-1/2 in. Deep Switch Boxes - Gangable with Conduit KO's **Plaster Ears**

A47





Catalog #: 8500

APPLICATIONS

RACO® Switch boxes are used to house wiring devices such as switches and outlets

PRODUCT FEATURES

Gangable switch boxes offer the option of constructing a box to hold two or more devices Plaster ears allow a box to be used in "old work" applications

UL LISTED

File E195978

COMPLIANCES

All RACO® single gang, two gang, 4 in. square, and single gang gangable UL listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult UL "Fire Resistance Directory" or the UL website at www.ul.com

FIRE RESISTANCE

Acceptable for use in 2-hour rated walls

GENERAL PRODUCT INFORMATION

Conduit Wiring System:

CONFIGURATION End Knockouts:

(2) 1/2 in. Ends Cable: No Bracket Bracket Type: Side Knockout(s): (4) 1/2 in. Bottom Knockouts(s) (2) 1/2 in.

DRAWING DIMENSIONS

Dimension A: 2-1/2 in.

PRODUCT MEASUREMENTS

Depth: 2-1/2 in. Cubic Inches (cm3): 12.5 (204.8) Wt. Ea. (Lbs.): 0.551 Product Length (in.): Product Width (in.): 2.50 4.22 Product Height (in.): 2.00

PACKAGING

Minimum Pack Qty.: Std. Pkg.: Product UPC-A Labeled: 25 25 Yes Weight (Lbs. Per/C): Ship Carton Length (in.): 55.10 18.25 Ship Carton Width (in.): 5.75 6.75 13.78 Ship Carton Height (in.): Ctn Weight (Lbs.): Pallet Qty: UPC Number: 2800 050169005002 12of5: 40050169005000

Page 1 / 1