

**4-11/16 IN. SQUARE EXPOSED WORK****4-11/16 in. Square Exposed Work Covers
30-50A Receptacle 2.141 in. Dia.****A29**

Catalog #: 878

APPLICATIONS

RACO® surface covers are used to support switches or receptacles in areas where the box is surface mounted or positioned in exposed work applications

PRODUCT FEATURES

RACO® exposed work covers include required hardware for mounting the receptacle(s)

RACO® exposed work covers meet the requirements of the 2014 NEC Article 250.146(A). No bonding jumper is required for covers with: (1) Crushed corners (2) Two or more device attachment screws (3) A lockwasher or equivalent

Hardware and cover are packed in a poly-bag with printed catalog number, compliances and installation instructions

UL LISTED

File E195978

GENERAL PRODUCT INFORMATION**PRODUCT MEASUREMENTS**

Cubic Inches (cm3):	10.3 (168.8)
Wt. Ea. (Lbs.):	0.536
Product Length (in.):	0.50
Product Width (in.):	4.69
Product Height (in.):	4.69

PACKAGING

Minimum Pack Qty.:	10
Std. Pkg.:	10
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	53.60
Ship Carton Length (in.):	10.00
Ship Carton Width (in.):	4.31
Ship Carton Height (in.):	5.25
Ctn Weight (Lbs.):	5.36
Pallet Qty:	2880
UPC Number:	050169008782
I2of5:	50050169008787