




CEILING FAN & FIXTURE SUPPORT PRODUCTS

KWIK-BRACE® - New Construction Braces for Lighting Fixtures or Ceiling Fans
1-1/2 in. Depth

A35



Catalog #: 926

APPLICATIONS

RACO® KWIK-BRACE® is a heavy-duty ceiling fan brace designed for new or existing construction where joists are accessible

PRODUCT FEATURES

- Slides apart to accommodate joist spacing from 16" to 24", screws provided
- #10-32, 1" long ceiling fan screws provided and #8-32 ceiling fixture mounting provisions
- Metal protection plate included
- Nail spurs for easy brace positioning
- Easy installation, up front ground screw
- Easy to follow instructions and mounting hardware included

UL LISTED

File E 195978

US PATENTS

7,148,420; 6,595,479; 7,191,994

RECOMMENDED MAX LOAD

| | | | | | | | |
|--|----|--|----|---|-----|---|----|
| Ceiling Fan (Dynamic) Lbs., 16 in. Joist Span: | 70 | Ceiling Fan (Dynamic) Lbs., 24 in. Joist Span: | 70 | Fixture (Static) Lbs., 16 in. Joist Span: | 210 | Fixture (Static) Lbs., 24 in. Joist Span: | 90 |
|--|----|--|----|---|-----|---|----|

| | |
|----------------------|-------------|
| Cable Priouts: | INSIDER® |
| Drawn or Welded: | Drawn |
| Raised Ground: | Yes |
| Side Knockout(s): | --- |
| Bottom Knockouts(s): | (3) 1/2 in. |

CONFIGURATION

PRODUCT MEASUREMENTS

| | |
|-----------------------|--------------|
| Depth: | 1-1/2 in. |
| Cubic Inches (cm3): | 15.8 (258.9) |
| Wt. Ea. (Lbs.): | 2.333 |
| Product Length (in.): | 15.13 |
| Product Width (in.): | 3.03 |
| Product Height (in.): | 4.25 |

PACKAGING

| | |
|---------------------------|----------------|
| Minimum Pack Qty.: | 6 |
| Std. Pkg.: | 6 |
| Product UPC-A Labeled: | Yes |
| Weight (Lbs. Per/C): | 233.30 |
| Ship Carton Length (in.): | 15.75 |
| Ship Carton Width (in.): | 9.25 |
| Ship Carton Height (in.): | 9.50 |
| Ctn Weight (Lbs.): | 14.00 |
| Pallet Qty: | 288 |
| UPC Number: | 050169009260 |
| I2of5: | 50050169009265 |