



* Representative image

Anchor Shackle

by ANDERSON
Catalog ID: 946693001

Shackle, Forged Steel, 1.188" Opening, 1.125" Bolt, UTS 100,000 lb

Product Details

General

| | |
|---------------------------------|------------------|
| Material | Steel |
| Material - Pin (Clevis) | Galvanized Steel |
| Material - Pin (Cotter) | Stainless Steel |
| Number of Bolt Holes | 0 |
| Series | AS Series |
| Strength Rating - Ultimate | 100000 lb |
| Strength Rating - Ultimate Body | 0 lb |
| UPC | 096359253211 |

Dimensions

| | |
|-------------------------------------|----------|
| Assembly Rating (Ultimate) | 0 lb |
| Clevis Opening | 1.188 in |
| Diameter - Bolt | 0 in |
| Diameter - Pin | 0 in |
| Insulator Throat Diameter - Maximum | 0 in |
| Insulator Throat Diameter - Minimum | 0 in |
| Length - Coupling | 4.313 in |
| Length - Pin | 0 in |
| Maximum Adjustment | 0 in |
| Ring Height | 0 in |
| Weight | 6.635 lb |

Conductor Related

| | |
|------------------------------|------|
| Conductor Diameter - Maximum | 0 in |
| Conductor Spacing | 0 in |

Logistics

| | |
|-----------------|--------|
| Pallet Quantity | 384 EA |
|-----------------|--------|

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com