



Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 75kVA

By Acme Electric
Catalog # [A3075K0310B](#)



Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 75kVA

Features

- Copper terminations for trouble free operation
- Lower cost solution
- 5-10 times increase in kVA

General

| | |
|----------------------|---------------------|
| Catalog Number | A3075K0310B |
| Construction | Encapsulated |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Wall |
| Secondary Voltage | 208 V |
| UPC | 047503006962 |
| Winding Material | AL |
| kVA | 75 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 11.14 in x 27.13 in x 24.81 in |
| Height | 24.81 in |
| Length | 11.14 in |
| Weight | 400 lb |

| | |
|-------|----------|
| Width | 27.13 in |
|-------|----------|

Electrical Ratings

| | |
|------------------|-------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 240 V |

Certifications And Compliance

| | |
|-------------|---------|
| Nema Rating | NEMA 3R |
|-------------|---------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
| Pallet Quantity | 4 |

Product Assets

- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - A3075K0310B](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - Product Information Video Series - 3 Phase Buck Boost](#)