



Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 150kVA

By Acme Electric
Catalog # A3150K0310B

Buck-Boost Transformer - Three Phase, 220/230/240 - 208V, 150kVA



*Representative Image

Features

- Copper terminations for trouble free operation
- Lower cost solution
- 5-10 times increase in kVA

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Secondary Voltage	208 V
UPC	047503006986
Winding Material	AL
kVA	150

Dimensions

Dimensions	11.14 in x 27.13 in x 24.81 in
Height	24.81 in
Length	11.14 in
Weight	650 lb
Width	27.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

Certifications And Compliance

Nema Rating	NEMA 3R
-------------	---------

Product Assets

[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)

[SDS - HCC SDS](#)

[Terms and Conditions - HCC Terms & Conditions](#)

[Video - Product Information Video Series - 3 Phase Buck Boost](#)



A Hubbell brand