



# Industrial Control Transformer .100KVA 240X480-120 F1

By Acme Electric  
Catalog # [CE100N008CF1](#)

ICT .100KVA 240X480-120 F1



## Features

- Encapsulated design protects core & coil assembly from potentially damaging contaminants
- Constructed with high quality silicon steel lamination to minimize core losses and increase efficiency
- Integrally molded terminal blocks with isolation barriers to prevent arc over
- Fuse blocks kits available and easily adaptable
- Series-parallel connecting links save wiring and labor costs

## Application

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

## General

Catalog Number                      [CE100N008CF1](#)

Color                                              Black  
Secondary Voltage                          120 V  
UPC                                                047503015414

## Dimensions

Dimensions                                    3.778 in x 3.375 in x 4.356 in  
Height                                         4.356 in  
Length                                         3.778 in  
Weight                                         4.2 lb  
Width                                         3.375 in

## Electrical Ratings

Primary Voltage                              240 X 480 V

## Certifications And Compliance

Certified Listed                              

- UL Listed
- cUL Listed

## Logistics

Carton Quantity                              1  
Pallet Quantity                                120

## Product Assets

[Specifications - CE100N008CF1](#)